





Swagelok Grab Sampling Data Sheet

Customer Information	
Date	
Customer Name	
Project Name	
Site Location	
Sample Location	
Customer Contact Name	
Customer Contact Email	
Customer Contact Phone	
Customer Need Date	
Media and System Data	
Fluid Phase	Gas <input type="checkbox"/> Liquid <input type="checkbox"/>
Sample Media(s)	
Design Pressure	Min = Max =
Operating Pressure	Min = Max =
Design Temperature	Min = Max =
Operating Temperature	Min = Max =
Sampling Options	
Grab Sample Module (GSM)	Grab Sample Liquid System (GSL)
<p>Cylinder: 150 cm³ <input type="checkbox"/> 300 cm³ <input type="checkbox"/> 400 cm³ <input type="checkbox"/> 500 cm³ <input type="checkbox"/> 1000 cm³ <input type="checkbox"/></p> 	<p>Boston Round: 8oz <input type="checkbox"/> 16oz <input type="checkbox"/> 32oz <input type="checkbox"/> Media Bottle: 250 cm³ <input type="checkbox"/> 500 cm³ <input type="checkbox"/> 1000 cm³ <input type="checkbox"/></p> 
Other Container Size: _____	



Sampling Options	
Continuous Flow	Yes <input type="checkbox"/> No <input type="checkbox"/>
Purge Type	Nitrogen <input type="checkbox"/> Water <input type="checkbox"/> Air <input type="checkbox"/> N/A <input type="checkbox"/> Other: _____
Sample Cooler	Yes <input type="checkbox"/> No <input type="checkbox"/>
Inlet/Outlet Connection Size	1/4" <input type="checkbox"/> 3/8" <input type="checkbox"/> 1/2" <input type="checkbox"/> 3/4" <input type="checkbox"/> 1" <input type="checkbox"/>
Vent Connection Size	1/4" <input type="checkbox"/> 3/8" <input type="checkbox"/> 1/2" <input type="checkbox"/> 3/4" <input type="checkbox"/> 1" <input type="checkbox"/>
Drain Connection Size	1/4" <input type="checkbox"/> 3/8" <input type="checkbox"/> 1/2" <input type="checkbox"/> 3/4" <input type="checkbox"/> 1" <input type="checkbox"/>
Preferred Wetted Materials	316 SS <input type="checkbox"/> Other: _____
Preferred Elastomers	Fluorocarbon FKM (Viton) <input type="checkbox"/> Perfluorocarbon FFKM (Kalrez) <input type="checkbox"/> Ethylene Propylene (EPDM) <input type="checkbox"/> Buna-N <input type="checkbox"/>
Assembly/Stand Options	
Assembly Type	Panel <input type="checkbox"/> Enclosure <input type="checkbox"/>
Panel/Enclosure Material	304 SS <input type="checkbox"/> Powder Coated Carbon Steel <input type="checkbox"/> Aluminium <input type="checkbox"/> Other: _____
Outside Sample Controls	N/A <input type="checkbox"/> Yes <input type="checkbox"/> No <input type="checkbox"/>
Mounting Options	Wall Mount <input type="checkbox"/> Stand Mount <input type="checkbox"/>
Stand Materials	Carbon Steel with Powder Coat <input type="checkbox"/> 304 SS <input type="checkbox"/> Other: _____
Heated Enclosure	Steam <input type="checkbox"/> Electric (C1D2 Gp ABCD T3/T4) <input type="checkbox"/> N/A <input type="checkbox"/>
Enclosure Vent	1/2" Tube to Atmosphere <input type="checkbox"/> Eductor Powered <input type="checkbox"/> N/A <input type="checkbox"/>
Enclosure Windows	Front <input type="checkbox"/> Back <input type="checkbox"/> Both <input type="checkbox"/> N/A <input type="checkbox"/>
Enclosure Drain	1/2" Ball Valve <input type="checkbox"/> None <input type="checkbox"/> N/A <input type="checkbox"/>
Additional Options	
Pressure Test	1.0 x Design, Nitrogen <input type="checkbox"/> 1.5 x Design, Nitrogen <input type="checkbox"/> Helium <input type="checkbox"/> Other: _____
NACE MR0103/ISO 17945 Components	Yes <input type="checkbox"/> No <input type="checkbox"/>
Include Material Test Reports (MTRs)	Yes <input type="checkbox"/> No <input type="checkbox"/>
Positive Material Identification	Yes <input type="checkbox"/> No <input type="checkbox"/>

For more information on our grab sampling capabilities contact us today.

Swagelok Minnesota | North Dakota | Appleton

800-422-6410

info@minnesota.swagelok.com

minn.swagelok.com

